




# HorolithForce



Powerful acidic cleaner for milking equipment and milk tanks.

- ▲ Excellent cleaning properties
- ▲ Perfect balance of three acids
- ▲ For challenging conditions

## APPLICATION

Pre-clean with water. Clean with **HorolithForce** at 0.5 - 1.0 % (minimum 10 min. at 40 - 50°C). Rinse with water of drinking quality. To be used in daily rotation with **AseptoForce**.



## FEATURES AND BENEFITS

**HorolithForce** is a well-balanced acidic product with excellent scale removing and cleaning properties. It is suitable for all kind of standard milking equipment, including cooling tanks. The **Force** products are specially developed for challenging cleaning conditions. The combination of dedicated ingredients assures best hygiene results.

## SPECIFICATIONS

HorolithForce	
Physical form	Colourless liquid
Active substance	Inorganic acids
pH at 20°C:	0.5 - 1.0
Density at 20°C (g/cm <sup>3</sup> ):	1.165 - 1.180
Storage temperature:	-20°C to +40°C

## LOGISTICS

Packaging	12 kg	23 kg	70 kg	240 kg
Product code	2332080	2332090	2334750	2332110
EAN code	4028162332087	4028162332094	4028162334753	4028162332117

A Material Safety Data Sheet is available on request for professional users.  
A Product Data Sheet is available on request.

**Ecolab Europe GmbH**  
Richtstrasse 7  
CH-8304 Wallisellen  
www.ecolab.com