



HorolithSupra

Powerful acidic cleaner for milking equipment and milk tanks.

- ▲ Very good performance in descaling
- ▲ Mixture of two acids

APPLICATION

Pre-clean with water. Clean with **HorolithSupra** at 0.5% (minimum 10 min. at 40 - 50°C). Rinse with water of drinking quality. To be used in daily rotation with **AseptoSupra**.



FEATURES AND BENEFITS

HorolithSupra is a mixture of two acids which assures very good scale removing and cleaning properties. It is suitable for all kind of standard milking equipment, including cooling tanks.

The **Supra** products are the widely applicable program providing great hygiene results.

SPECIFICATIONS

HorolithSupra	
Physical Form	Clear, colourless liquid
Active Substance	Inorganic acids
pH at 20°C:	1.0
Density at 20°C (g/cm3):	1.20 - 1.22
Storage temperature:	-30°C to +40°C

LOGISTICS

Packaging	12 kg	24 kg	72 kg	250 kg
Product code	2332160	2332170	2334770	2332190
EAN code	4028162332162	4028162332179	4028162334777	4028162332193

A Material Safety Data Sheet is available on request for professional users.
A Product Data Sheet is available on request.

Ecolab Europe GmbH
Richtistrasse 7
CH-8304 Wallisellen
www.ecolab.com